Product datasheet

Specifications





Mounting plate in galvanized steel, thickness 15 mm For boxes of H175W150 mm

Local distributor code: 387529068

NSYAMPM1916TB

EAN Code: 3606480166082

Main

Range	Thalassa	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Back studs	
Mounting Plate Description	Plain	
Range Compatibility	Thalassa Thalassa TBS Thalassa Thalassa TBP	
Device Composition	1 mounting plate	
Material	Galvanised steel	

Complementary

Fixing Mode	By screws - screw type M4 self tapping - on back studs location
Height	192 mm nominal: 140 mm real:
Width	164 mm nominal: 1685 mm real:
Thickness	1.5 mm
Net Weight	0.1 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	14.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	260.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.0 cm
Package 2 Width	4.0 cm
Package 2 Length	10.0 cm

Package 2 Weight

2.6 kg

Contractual warranty

Warranty

18 months

3 May 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations