Product datasheet





ClimaSys standard cooling unit side of enclosure - 1250W at 230

Local distributor code:

402654261 NSYCU1K2

! Discontinued on: 23 Nov 2023

! End-of-service on: 23 Feb 2024

EAN Code: 3606480620829

Overview

Lead Time Usually Ships within 4 Weeks

Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	230 V AC at 50/60 Hz, 1 phase	
Rated Power	1250 W	
Cooling Power	1250 W 50/60 Hz L35-L35 910 W 50/60 Hz L35-L50	

Complementary

Height	999 mm
Width	405 mm
Depth	237 mm
[In] Rated Current	3.8 A
Inrush Current	11 A
Power Consumption In W	650 W at 50/60 Hz, L35-L35 760 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	1.9
Control Type	Electronic controller
Temperature Setting Range	2055 °C at 50 Hz 2050 °C at 60 Hz
Ambient Air Temperature For Operation	2046 °C inside the enclosure: 55 °C maximum: 2055 °C at 50 Hz outside the enclosure: 2050 °C at 60 Hz outside the enclosure:
Noise Level	65 dB conforming to EN/ISO 3746

Life Is On Schneider 4 May 2024

Pressure	25 bar	
Flow Rate	Internal circuit: 570 m3/h at 50/60 Hz External circuit: 860 m3/h at 50/60 Hz	
Net Weight	38 kg	
Cooling Gas Type	R134a (0.38 kg)	
Type Of Filter	Optional external circuit filter	
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):	
Material	Steel	
Colour	Grey (RAL 7035)	

Environment

Product Certifications	CE
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery
Standards	EN/ISO 12100 EN 378 EN 60335-1 EN 60204-1 EN 60335-2-40
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	40.5 cm
Package 1 Length	99.9 cm
Package 1 Weight	38.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	5
Package 2 Height	125.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	227.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information