# **Product datasheet**





## ClimaSys standard cooling unit roof of enclosure - 2900W at 400 V

Local distributor code:

402654494

NSYCU3K3P4R

! Discontinued on: 23 Nov 2023

! End-of-service on: 23 Feb 2024

! Discontinued

EAN Code: 3606480620966

#### Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Roof of enclosure	
Installation	Indoor roof	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	400 V AC at 50/60 Hz, 3 phases	
Rated Power	2900 W	
Cooling Power	2900 W 50/60 Hz L35-L35 2250 W 50/60 Hz L35-L50	

## Complementary

•		
Height	496 mm	
Width	797 mm	
Depth	492 mm	
[In] Rated Current	2.5 A	
Inrush Current	15.7 A	
Power Consumption In W	W 1210 W at 50/60 Hz, L35-L35 1450 W at 50/60 Hz, L35-L50	
Energy Efficiency Ratio	2.4	
Control Type	Electronic controller	
Temperature Setting Range	2050 °C	
Ambient Air Temperature For Operation	50 °C maximum: 2046 °C inside the enclosure: 2050 °C outside the enclosure:	
Noise Level	75 dB conforming to EN/ISO 3746	
Pressure	25 bar	
Flow Rate	Internal circuit: 860 m3/h at 50/60 Hz External circuit: 3410 m3/h at 50/60 Hz	
Net Weight	83 kg	
ooling Gas Type R134a (1.2 kg)		

Type Of Filter	Optional external circuit filter	
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):	
Material	terial Steel	
Colour	Grey (RAL 7035)	

## **Environment**

<b>Product Certifications</b>	CE	
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery	
Standards	EN 60204-1 EN 60335-2-40 EN 60335-1 EN 378 EN/ISO 12100	
Ip Degree Of Protection	IP34 conforming to IEC 60529 (on the external circuit) IP54 conforming to IEC 60529 (on the internal circuit)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.2 cm
Package 1 Width	49.6 cm
Package 1 Length	79.7 cm
Package 1 Weight	83.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	152.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	213.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information