# **Product datasheet**

Specifications

 <u>
Green</u> <u>
Premium</u><sup>™</sup>



ClimaSys standard cooling unit side of enclosure - 380W at 230 V

402654643

NSYCU400

() Discontinued on: 23 Nov 2023

(!) End-of-service on: 23 Feb 2024

#### EAN Code: 3606480620775

#### Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Cooling unit
Mounting Type	Side
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	380 W
Cooling Power	380 W 50/60 Hz L35-L35 240 W 50/60 Hz L35-L50

### Complementary

Height	460 mm
Width	285 mm
Depth	180 mm
[In] Rated Current	1.6 A
Inrush Current	6 A
Power Consumption In W	280 W at 50/60 Hz, L35-L35 330 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	1.4
Control Type	Electronic controller
Temperature Setting Range	2055 °C at 50 Hz 2050 °C at 60 Hz
Ambient Air Temperature For Operation	2046 °C inside the enclosure: 55 °C maximum: 2055 °C at 50 Hz outside the enclosure: 2050 °C at 60 Hz outside the enclosure:
Noise Level	60 dB conforming to EN/ISO 3746
Pressure	26 bar
Flow Rate	Internal circuit: 280 m3/h at 50/60 Hz External circuit: 280 m3/h at 50/60 Hz
Net Weight	17 kg

Cooling Gas Type	R134a (0.16 kg)		
Type Of Filter	Optional external circuit filter	Optional external circuit filter	
Protection Type	Thermal protection: T 4 A Short-circuit protection (magnetic):		
Material	Steel		
Colour	Grey (RAL 7035)		

## Environment

Product Certifications	CE
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery
Standards	EN 378 EN 60335-2-40 EN 60204-1 EN/ISO 12100 EN 60335-1
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.0 cm
Package 1 Width	28.5 cm
Package 1 Length	46.0 cm
Package 1 Weight	17.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	16
Package 2 Height	126.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	326.0 kg

### Logistical informations

Country Of Origin

US

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information