# **Product datasheet**





### ClimaSys standard cooling unit side of enclosure - 1250W at 400...440 V

Local distributor code: 402657019

NSYCUX1K22P4

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3606480653698

#### Main

Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	400460 V AC at 50/60 Hz, 2 phases	
Rated Power	1250 W	
Cooling Power	1250 W 50/60 Hz L35-L35 910 W 50/60 Hz L35-L50	

### Complementary

J		
Height	<b>ht</b> 999 mm	
Width	405 mm	
Depth	237 mm	
[In] Rated Current	2.8 A	
Inrush Current	8.5 A	
Power Consumption In W	660 W at 50/60 Hz, L35-L35 770 W at 50/60 Hz, L35-L50	
Energy Efficiency Ratio 1.9		
Control Type	Electronic controller	
Temperature Setting Range	2050 °C	
Ambient Air Temperature For Operation	50 °C maximum: 2046 °C inside the enclosure: 2050 °C outside the enclosure:	
Noise Level	65 dB conforming to EN/ISO 3746	
Pressure	25 bar	
Flow Rate	Internal circuit: 570 m3/h at 50/60 Hz External circuit: 860 m3/h at 50/60 Hz	
Net Weight	40 kg	
Cooling Gas Type	R134a (0.38 kg)	
Type Of Filter Optional external circuit filter		

Protection Type	Thermal protection: T 4 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Grey (RAL 7035)

#### **Environment**

Product Certifications	CE	
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive 2006/42/EC - machinery	
Standards	EN 60335-1 EN/ISO 12100	
	EN 60204-1	
	EN 60335-2-40	
	EN 378	
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit)	
	IP34 conforming to IFC 60529 (on the external circuit)	

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	40.5 cm
Package 1 Length	99.9 cm
Package 1 Weight	40.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	5
Package 2 Height	123.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	221.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information