# **Product datasheet**

Specification





# ClimaSys standard cooling unit side of enclosure - 640W at 230 V

NSYCUX600

Local distributor code:

402657190

! Discontinued on: 9 Feb 2023

EAN Code: 3606480653544

Main		
Range	ClimaSys	
Product Name	CU	
Product Or Component Type	Cooling unit	
Mounting Type	Side	
Installation	Indoor side	
Product Destination	For enclosure	
Mounting Mode	By screws	
Supply Voltage	230 V AC at 50/60 Hz, 1 phase	
Rated Power	640 W	
Cooling Power	640 W 50/60 Hz L35-L35 470 W 50/60 Hz L35-L50	

### Complementary

· · · · · · · · · · · · · · · · · ·		
Height	606 mm	
Width	316 mm	
Depth	212 mm	
[In] Rated Current	2.1 A	
Inrush Current	8.1 A	
Power Consumption In W	<b>ption In W</b> 400 W at 50/60 Hz, L35-L35 470 W at 50/60 Hz, L35-L50	
ergy Efficiency Ratio 1.6		
Control Type	Electronic controller	
Temperature Setting Range	2055 °C at 50 Hz 2050 °C at 60 Hz	
Ambient Air Temperature For Operation	2046 °C inside the enclosure: 55 °C maximum: 2055 °C at 50 Hz outside the enclosure: 2050 °C at 60 Hz outside the enclosure:	
Noise Level	65 dB conforming to EN/ISO 3746	
Pressure	25 bar	
Flow Rate	Internal circuit: 330 m3/h at 50/60 Hz External circuit: 570 m3/h at 50/60 Hz	
Net Weight	21 kg	
Cooling Gas Type	R134a (0.23 kg)	

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Grey (RAL 7035)

#### **Environment**

Product Certifications	CE	
Directives	2006/95/EC - low voltage directive 2006/42/EC - machinery 2004/108/EC - electromagnetic compatibility	
Standards	EN 60335-1 EN/ISO 12100 EN 60335-2-40 EN 378 EN 60204-1	
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.2 cm
Package 1 Width	31.6 cm
Package 1 Length	60.6 cm
Package 1 Weight	23.2 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	85.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	160.4 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information