## **Product datasheet**

Specifications





# Climasys forced vent. 170 m3/h, 115V without grille

NSYCVF170M115

Local distributor code:

385510998

EAN Code: 3606480151439

### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Flow Rate	Free flow rate: 170 m3/h at 50 Hz
Input Voltage	115 V 50/60 Hz

## Complementary

Absorbed Power	17 W
Noise Level < At	41 dB
Height	External: 119 mm
Width	External: 119 mm
Depth	External : 38 mm
Net Weight	0.82 kg
Material	Protective grille: steel
<b>Device Composition</b>	axial motor     protective grille: on the front and rear surfaces     fixing collar

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.096 cm
Package 1 Width	14.986 cm
Package 1 Length	17.018 cm
Package 1 Weight	848.226 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	20 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8.84 kg

## **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information