

NSYCVF35M115


Local distributor code:

398244277



! Discontinued on: 9 Feb 2023

EAN Code: 3606480151491



Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan motor
Flow Rate	Free flow rate: 35 m3/h at 50 Hz
Input Voltage	115 V 50/60 Hz

Complementary

Absorbed Power	16 W 50 Hz 14 W 60 Hz
Noise Level < At	32 dB
Height	80 mm external:
Width	80 mm external:
Depth	25 mm external:
Cut-Out Dimensions	Ø 78 mm
Device Composition	1 axial motor

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	10.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	150.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information