Product datasheet

Specification





ClimaSys forced vent. IP54, 38m3/ h, 115V, with outlet grille and filter G2

Local distributor code:

388829181 NSYCVF38M115PF

EAN Code: 3606480151170

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 38 m3/h at 50 Hz Free flow rate with standard filter: 39 m3/h at 60 Hz
[Us] Rated Supply Voltage	75125 V
Input Voltage	115 V 50/60 Hz

Complementary

3.3 W 50 Hz
3.5 W 60 Hz
0.16 A 50 Hz
0.16 A 60 Hz
4041 dB
Ball
External: 137 mm
External: 117 mm
External : 49 mm
92 x 92 mm
0.22 kg
Outlet grille: injected thermoplastic (ASA PC)
Outlet grille: grey (RAL 7035)
-1070 °C
-4070 °C
29 Pa flow rate 0 m³/h
Cable
IP54
1 axial motor
2 protective grille: on the front and rear surfaces
1 filter: front of axial motor

1 outlet grille: front 1 cut-out template Condition Of Use Outside temperature must be 5 °C lower than inside temperature

Flow rates depends on the work point, see ProClima software

Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Filter must be cleaned and replaced regularly

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	12.5 cm
Package 1 Length	15.0 cm
Package 1 Weight	292.0 g
Unit Type Of Package 2	PAM
Number Of Units In Package 2	340
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	80 cm
Package 2 Weight	128 kg

Contractual warranty

Warranty 18 months

18 May 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information