

Product datasheet

Specifications



ClimaSys forced vent. IP54, 38m3/h, 230V, with outlet grille and filter G2

NSYCVF38M32

EAN Code: 3606480274350

! Discontinued

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 38 m3/h at 50 Hz
Input Voltage	230 V AC 50/60 Hz

Complementary

Height	137 mm external:
Width	117 mm external:
Depth	150 mm external:
Cut-Out Dimensions	92 x 92 mm
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7032)
Connections - Terminals	Cable
Ip Degree Of Protection	IP54
Device Composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template 1 power cord
Condition Of Use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)