# **Product datasheet**





## ClimaSys CVHD outdoor HD fanbox without grille and filter 550 m3/ h 115VAC

Local distributor code: 402657255

NSYCVF550M115FB

! Discontinued on: 9 Feb 2023

! Discontinued

EAN Code: 3606480678776

#### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fanbox without grille and filter
Application	Outdoor heavy duty
Range Compatibility	Thalassa PHD Spacial S3HD Spacial SFHD
Flow Rate	Free flow rate: 550 m3/h at 50 Hz 550 m3/h at 60 Hz
[Us] Rated Supply Voltage	115 V AC +/- 10 %
Input Voltage	115 V AC 50/60 Hz
Certification	CE UL conforming to UL 508 A CSA conforming to CSA C22.2 Ecodesign directive 2009/125/EC

### Complementary

Absorbed Power	78102 W
[In] Rated Current	0.70.8 A 50 Hz
Noise Level < At	60 dB
Bearing Type	Ball
Height	External: 223 mm
Width	External: 223 mm
Depth	External : 90 mm
Net Weight	1.7 kg
Colour	Dark grey (RAL 7016)
Ambient Air Temperature For Operation	-4070 °C
Ambient Air Temperature For Storage	-4080 °C
Maximum Pressure	300 Pa flow rate 0 m³/h
Connections - Terminals	Spring clamp terminal
Ip Degree Of Protection	IP55 grid: IP44
Device Composition	1 fanbox 4 screw

Condition Of Use Overfrequent filter replacement should be avoided

Flow rates depends on the work point, see ProClima software

Surrounding environment must be relatively clean Filter must be cleaned and replaced regularly

Outside temperature must be 5 °C lower than inside temperature

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	15.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	2.0 kg

### **Logistical informations**

Country Of Origin

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information