

Product datasheet

Specifications



Plain right door Spacial CRNG H1000xW600 RAL 7035 with lock

NSYDCRNG106R

EAN Code: 3606480491535

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Right door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial CRN
Device Composition	1 door locking system
Quantity Per Set	Set of 1

Complementary

Material	Door: sheet steel
Colour	Grey (RAL 7035)
Surface Finish	Textured epoxy polyester
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	Plain
Door Opening Side	Reversible (120 °)
Maximum Load	50 kg/m²
Height	Nominal: 1000 mm Real: 1020 mm
Width	Nominal: 600 mm
Net Weight	11.594 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	61.0 cm
Package 1 Length	102.0 cm
Package 1 Weight	11.594 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information