


Product datasheet

Specifications



Monobloc perforated plates H1000xW600mm with universal perforations 11x26mm

Local distributor code:

392865568

NSYMR106

EAN Code: 3606480183553

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 1000 mm W: 600 mm
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Telequick perforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Zinc coated

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Height	945 mm
Width	551 mm
Depth	15 mm
Thickness	2 mm
Net Weight	4.04 kg
Number Of Slots	1088
Variant Particularity	Installation in rear of enclosure
Cut-Out Dimensions	11 x 26 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	55.5 cm
Package 1 Length	94.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	3.818 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	100
Package 2 Height	89 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	398.5 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations