



# Monobloc perforated plates H1000xW800mm with universal perforations 11x26mm

Local distributor code:
392865571 NSYMR108

EAN Code: 3606480183560

### Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- - H: 1000 mm W: 800 mm	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Telequick perforated	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	Steel	
Surface Finish	Zinc coated	

### **Complementary**

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Height	945 mm	
Width	751 mm	
Depth	15 mm	
Thickness	2 mm	
Net Weight	4.96 kg	
Number Of Slots	1536	
Variant Particularity	Installation in rear of enclosure	
Cut-Out Dimensions	11 x 26 mm	

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	75.0 cm
Package 1 Length	95.0 cm

Package 1 Weight	4.98 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	76
Package 2 Height	91.0 cm
Package 2 Width	100.5 cm
Package 2 Length	120.0 cm
Package 2 Weight	407.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations