



Monobloc perforated plates H1200xW1000mm with universal perforations 11x26mm

Local distributor code: 392865623 NSYMR1210

EAN Code: 3606480183577

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 1200 mm W: 1000 mm	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Telequick perforated	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Per Set Set of 1	
Material	Steel	
Surface Finish	Zinc coated	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Permanent Permissible Load	272.2 kg S3D, CRN, S3X enclosures 163.3 kg PLM enclosure	
Maximum Load	250 kg S3D, CRN, S3X enclosures 150 kg PLM enclosure	
Height	1145 mm	
Width	951 mm	
Surface And Useful Surface	108.9 dm²	
Thickness	2 mm	
Net Weight	7.8 kg	
Number Of Slots	2325	
Variant Particularity	Installation in rear of enclosure	
Cut-Out Dimensions	11 x 26 mm	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	115.0 cm	
Package 1 Width	95.2 cm	
Package 1 Length	1.7 cm	
Package 1 Weight	7.8 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations