



Silkscreened plain mounting plate H600xW400mm made of galvanised sheet steel

Local distributor code: 398249434

NSYMS64

! Discontinued on: 7 Aug 2023

! Discontinued

EAN Code: 3606480199097

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 600 mm W: 400 mm	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Plain	
Range Compatibility	patibility Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	Galvanised steel	
Surface Finish	sh Silkscreened	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Permanent Permissible Load	90 kg	
Height	550 mm	
Width	350 mm	
Depth	125 mm	
Thickness	1.8 mm	
Net Weight	4 kg	
Variant Particularity	Centimetric grid pattern	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	35.5 cm
Package 1 Length	55.0 cm

Package 1 Weight	2.718 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	140
Package 2 Height	37.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	394.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations