



# Internal door for Spacial WM encl. H700xW500 steel, RAL7035.Adjustable in depth

Local distributor code: 392869975 NSYPIN75

EAN Code: 3606480168543

#### Main

| Range                                 | Spacial                                                           |
|---------------------------------------|-------------------------------------------------------------------|
| Accessory / Separate Part<br>Category | Enclosure accessory                                               |
| Product Or Component Type             | Door                                                              |
| Application                           | Multi-purpose                                                     |
| For Enclosure Nominal Dimensions      | -                                                                 |
| Mounting Location                     | Front side<br>Step slide                                          |
| Range Compatibility                   | Spacial Spacial CRN<br>Spacial Spacial S3D<br>Spacial Spacial S3X |
| Device Composition                    | 1 door<br>4 fixing brackets<br>2 mounting uprights                |

### Complementary

| Material          | Door: sheet steel            |
|-------------------|------------------------------|
| Colour            | All faces: grey (RAL 7035)   |
| Surface Finish    | Polyester powder             |
| Lock Type         | Lock 3 mm double bar         |
| Number Of Locks   | 1                            |
| Adjustment        | Pitch 25 mm (on step slides) |
| Door Type         | Internal plain               |
| Door Opening Side | Reversible                   |
| Maximum Load      | 30 kg/m²                     |
| Height            | Nominal: 700 mm              |
| Width             | Nominal: 500 mm              |
| Net Weight        | 5.6 kg                       |

### **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 4.500 cm  |
| Package 1 Width              | 45.500 cm |
| Package 1 Length             | 67.000 cm |

| Package 1 Weight             | 5.641 kg   |
|------------------------------|------------|
| Unit Type Of Package 2       | P12        |
| Number Of Units In Package 2 | 10         |
| Package 2 Height             | 45.000 cm  |
| Package 2 Width              | 80.000 cm  |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 68.410 kg  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)                                          |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile                                                                       |
| Circularity Profile      | No need of specific recycling operations                                                            |