Product datasheet





Floor standing enclosure polyester vers.PLA completely sealed 1000x500x320 IP65

Local distributor code:

403419609

NSYPLA1053G

EAN Code: 3606480774430

Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLA
Nominal Height	1000 mm
Nominal Width	500 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	4 points lock, 5 mm double-bar
Accessibility For Operation	Front Rear
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Nema Degree Of Protection	NEMA 13 NEMA 12 NEMA 3S NEMA 2 NEMA 1 NEMA 5 NEMA 5 NEMA 3X NEMA 3 NEMA 3
Product Certifications	Veritas DNV Marine UL/cUL listed

Electrical Insulation Class Class II

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529 (completely sealed)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	38.0 cm
Package 1 Width	53.0 cm
Package 1 Length	102.0 cm
Package 1 Weight	21.5 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	5
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	115 cm
Package 2 Weight	123 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations