Product datasheet

Specifications





Floor standing enclosure polyester vers.PLA completely sealed 1250x500x320 IP65

Local distributor code: 403419683

NSYPLA1253G

EAN Code: 3606480774591

Main

| Range | Thalassa |
|---------------------------|--|
| Product Name | Thalassa PLA |
| Enclosure Type | Multi-purpose |
| Product Or Component Type | Suitable enclosure |
| Version | PLA |
| Nominal Height | 1250 mm |
| Nominal Width | 500 mm |
| Nominal Depth | 320 mm |
| Enclosure Mounting | Floor-standing |
| Device Composition | 1 top part 1 bottom part 2 side part 1 rear panel 1 door |

Complementary

| Body Type | Sealed top and bottom part assembled with side parts |
|-----------------------------|--|
| Door Type | Plain front |
| Number Of Doors | 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 4 points lock, 5 mm double-bar |
| Accessibility For Operation | Front Rear |
| Removable Parts | Door by hinges Rear panel by fixing element |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey (RAL 7035) |
| Standards | UL 508 A IEC 62208 |
| Nema Degree Of Protection | NEMA 3S NEMA 12 NEMA 2 NEMA 5 NEMA 1 NEMA 3X NEMA 33 |

| Product Certifications | UL/cUL listed Veritas DNV Marine |
|-----------------------------|--|
| Electrical Insulation Class | Class II |

Environment

| Ip Degree Of Protection | IP65 conforming to IEC 60529 (completely sealed) |
|--|--|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 (plain door) |
| Fire Resistance | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Storage | -3590 °C |

Packing Units

| - | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 126.0 cm |
| Package 1 Width | 54.0 cm |
| Package 1 Length | 38.0 cm |
| Package 1 Weight | 28.681 kg |
| Unit Type Of Package 2 | РАМ |
| Number Of Units In Package 2 | 5 |
| Package 2 Height | 120 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 140 cm |
| Package 2 Weight | 142 kg |
| | |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |