Product datasheet

Specifications

Green Premium[™]



Floor standing encl. polyester vers.PLA compl.sealed 750x750x620 IP65 glazed

NSYPLA776TG

EAN Code: 3606485434469

Main

Thalassa
Thalassa PLA
Multi-purpose
Suitable enclosure
PLA
750 mm
750 mm
620 mm
Floor-standing
1 top part 1 bottom part 2 side part 1 rear panel 1 door

Complementary

Body Type	Sealed top and bottom part assembled with side parts
Door Type	Transparent front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	2 points lock, 5 mm double-bar
Accessibility For Operation	Front Rear
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Nema Degree Of Protection	NEMA 5 NEMA 13 NEMA 3S NEMA 3X NEMA 2 NEMA 12 NEMA 3 NEMA 1

Product Certifications	DNV Marine UL/cUL listed Veritas
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529 (completely sealed)
Ik Degree Of Protection	IK08 conforming to IEC 62262 (glazed door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	78.0 cm
Package 1 Width	78.0 cm
Package 1 Length	65.0 cm
Package 1 Weight	29.49 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	130 cm
Package 2 Width	100 cm
Package 2 Length	90 cm
Package 2 Weight	79 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations