# **Product datasheet**





## Floor standing encl. polyester vers.PLAT open top w/ canopy 1000x1250x420 IP44

Local distributor code: 403420782

NSYPLAT10124G

! Discontinued on: 9 Feb 2023

! Discontinued

EAN Code: 3606480775185

#### Main

Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAT
Nominal Height	1000 mm
Nominal Width	1250 mm
Nominal Depth	420 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy

### Complementary

Body Type	Open top and sealed bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (120 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Front
	Тор
	Rear
Removable Parts	Door by hinges
	Rear panel by fixing element
	Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

#### **Environment**



Ip Degree Of Protection	IP44 conforming to IEC 60529 (with ventilated canopy)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	129.0 cm
Package 1 Width	100.0 cm
Package 1 Length	48.0 cm
Package 1 Weight	63.709 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	130 cm
Package 2 Width	100 cm
Package 2 Length	117 cm
Package 2 Weight	119 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations