Product datasheet

Specifications





Floor standing encl.polyester vers.PLAZ w/plinth open bottom 1500x1000x420 IP54

Local distributor code:

403422159

NSYPLAZ15104G

EAN Code: 3606480775727

Main

| Range | Thalassa |
|---------------------------|---|
| Product Name | Thalassa PLA |
| Enclosure Type | Multi-purpose |
| Product Or Component Type | Suitable enclosure |
| Version | PLAZ |
| Nominal Height | 1500 mm |
| Nominal Width | 1000 mm |
| Nominal Depth | 420 mm |
| Enclosure Mounting | Floor-standing |
| Device Composition | 1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 plinth |

Complementary

| Body Type | Sealed top and open bottom part assembled with side parts |
|-----------------------------|---|
| Door Type | Plain front |
| Number Of Doors | 2 door(s) |
| Door Opening Side | Right and left (120 °) |
| Lock Type | 4 points lock, handle with 5 mm double bar insert |
| Accessibility For Operation | Bottom Rear Front |
| Removable Parts | Door by hinges Rear panel by fixing element |
| Material | Polyester reinforced with fibreglass |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | Veritas |
| Electrical Insulation Class | Class II |

Environment

Ip Degree Of Protection

IP54 conforming to IEC 60529 (plinth type open bottom)

| Ik Degree Of Protection | IK10 conforming to IEC 62262 (plain door) |
|-------------------------------------|---|
| Fire Resistance | 960 °C conforming to IEC 62208 |
| Ambient Air Temperature For Storage | -3590 °C |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 165.6 cm |
| Package 1 Width | 48 cm |
| Package 1 Length | 103 cm |
| Package 1 Weight | 77.841 kg |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 120 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 168 cm |
| Package 2 Weight | 140 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |