# **Product datasheet**

Specifications





### Floor standing encl.polyester vers.PLAZ w/plinth open bottom 750x1250x420 IP54

Local distributor code: 403422052

NSYPLAZ7124G

#### () Discontinued on: 9 Feb 2023

(!) Discontinued

EAN Code: 3606480775901

#### Main

Thalassa
Thalassa PLA
Multi-purpose
Suitable enclosure
PLAZ
750 mm
1250 mm
420 mm
Floor-standing
1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 plinth

#### Complementary

Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (120 °)
Lock Type	2 points handle lock, 5 mm double-bar
Accessibility For Operation	Bottom Front Rear
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

### Environment

Ip Degree Of Protection	IP54 conforming to IEC 60529 (plinth type open bottom)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

### **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	81.5 cm
Package 1 Width	128.0 cm
Package 1 Length	45.0 cm
Package 1 Weight	46.334 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	4
Package 2 Height	129 cm
Package 2 Width	100 cm
Package 2 Length	174 cm
Package 2 Weight	154 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations