Product datasheet

Specifications

Green Premium[™]



Floor standing encl.polyester vers.PLAZ w/plinth open bottom 750x750x620 IP54

NSYPLAZ776G

() Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3606485434407

Main

Thalassa
Thalassa PLA
Multi-purpose
Suitable enclosure
PLAZ
750 mm
750 mm
620 mm
Floor-standing
1 top part 1 bottom part 2 side part 1 rear panel 1 door 1 plinth

Complementary

Body Type	Sealed top and open bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	2 points handle lock, 5 mm double-bar
Accessibility For Operation	Rear Bottom Front
Removable Parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP54 conforming to IEC 60529 (plinth type open bottom)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	81.5 cm
Package 1 Width	78.0 cm
Package 1 Length	65.0 cm
Package 1 Weight	31.0 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	2
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	182 cm
Package 2 Weight	76 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations