Product datasheet

Specification





Floor standing encl.polyester vers.PLAZT w/open plinth+canopy 1000x1250x320 IP44

Local distributor code:

403422489

NSYPLAZT10123G

EAN Code: 3606480775970

Main

-	
Range	Thalassa
Product Name	Thalassa PLA
Enclosure Type	Multi-purpose
Product Or Component Type	Suitable enclosure
Version	PLAZT
Nominal Height	1000 mm
Nominal Width	1250 mm
Nominal Depth	320 mm
Enclosure Mounting	Floor-standing
Device Composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel 1 canopy 1 plinth

Complementary

Body Type	Open top and bottom part assembled with side parts
Door Type	Plain front
Number Of Doors	2 door(s)
Door Opening Side	Right and left (180 °)
Lock Type	4 points lock, handle with 5 mm double bar insert
Accessibility For Operation	Rear
	Bottom
	Тор
	Front
Removable Parts	Door by hinges
	Rear panel by fixing element
	Canopy by fixing element
Material	Polyester reinforced with fibreglass
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	Veritas
Electrical Insulation Class	Class II

Environment



Ip Degree Of Protection	IP44 conforming to IEC 60529 (with plinth type open bottom part and ventilated canopy)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door)
Fire Resistance	960 °C conforming to IEC 62208
Ambient Air Temperature For Storage	-3590 °C

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	128.5 cm
Package 1 Width	37.0 cm
Package 1 Length	10.9 cm
Package 1 Weight	52.5 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	132 cm
Package 2 Width	100 cm
Package 2 Length	122 cm
Package 2 Weight	118 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations