

Product datasheet

Specifications



wall-mounting enclosure polyester
monobloc IP66
H430xW330xD200mm glazed
door

Local distributor code:
403422654

NSYPLM43TG

EAN Code: 3606480776540

Main

Range	Thalassa
Product Name	Thalassa PLM
Device Short Name	PLM
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	430 mm
Nominal Width	330 mm
Nominal Depth	200 mm
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 door 2 lock
Door Type	Transparent
Lock Type	3 mm double-bar lock

Complementary

Number Of Locks	2
Mounting Plate Description	Without mounting plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Body: polyester reinforced with fibreglass Door: tempered glass
Colour	Grey (RAL 7035)
Standards	NEMA classification 13 IEC 62208 NEMA classification 4X
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C conforming to IEC 62208

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-40...80 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	23.0 cm
Package 1 Length	46.0 cm
Package 1 Weight	5.905 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	50
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	191 cm
Package 2 Weight	315 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations