# **Product datasheet**

Specifications





# Telequick mounting plate for PLA enclosure H500xW500mm

Local distributor code: 385513678

NSYPMR55

EAN Code: 3606480194276

#### Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Back inserts Step slide
Mounting Plate Description	Telequick perforated
Range Compatibility	Thalassa Thalassa PLA Thalassa Thalassa PHD
Device Composition	1 mounting plate
Material	Galvanised steel

#### Complementary

Fixing Mode	By screws - screw type M8 - on back inserts location
	,
Permanent Permissible Load	150 kg
Height	Nominal: 500 mm
	Real: 370 mm
Width	Nominal: 500 mm
	Real: 376 mm
Depth	Real : 15 mm
Net Weight	1.4 kg
Cut-Out Dimensions	11 x 26 mm

#### **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	37.0 cm
Package 1 Length	37.5 cm
Package 1 Weight	1.142 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	150

Package 2 Height	50.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	184.0 kg

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations