Product datasheet

Specification





Spacial S3D plain door with mount.plate. H1000xW1000xD300 IP66 IK10 RAL7035.

Local distributor code:

392867207

NSYS3D101030P

EAN Code: 3606480160301

Main

Range	Spacial	
Product Name	Spacial S3D	
Application	Multi-purpose	
Category	Compact enclosure	
Enclosure Nominal Height	1000 mm	
Enclosure Nominal Width	1000 mm	
Enclosure Nominal Depth	300 mm	
Door Type	Plain	
Mounting Plate Description	Plain	
Type Of Gland Plate	Standard	
Installation Accessory Type	Wall-mounting	
Device Composition	body cable gland plate mounting plate door with lock	

Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure: steel Mounting plate: galvanised steel
Surface Finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
Product Certifications	DNV UL BV GL cUL LR

Net Weight 63 kg

Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.0 cm
Package 1 Width	101.0 cm
Package 1 Length	103.0 cm
Package 1 Weight	60.8 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	3
Package 2 Height	115.0 cm
Package 2 Width	103.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	195.6 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations