

# Product datasheet

Specifications



## Spacial S3D plain door with mount.plate. H1200xW600xD300 IP66 IK10 RAL7035.

Local distributor code:  
392866965

NSYS3D12630P

EAN Code: 3606480159930

### Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1200 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	300 mm
Door Type	Plain
Mounting Plate Description	Plain
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 mounting plate 1 door with lock 1 cable gland plate

### Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Enclosure: steel Mounting plate: galvanised steel
Surface Finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL GL BV DNV cUL LR

---

Net Weight	47.2 kg
------------	---------

## Environment

---

Nema Degree Of Protection	NEMA 4X/13
---------------------------	------------

---

Ik Degree Of Protection	IK10 conforming to IEC 62262
-------------------------	------------------------------

---

Ip Degree Of Protection	IP66 conforming to IEC 60529
-------------------------	------------------------------

## Packing Units

---

Unit Type Of Package 1	PCE
------------------------	-----

---

Number Of Units In Package 1	1
------------------------------	---

---

Package 1 Height	123.5 cm
------------------	----------

---

Package 1 Width	62.0 cm
-----------------	---------

---

Package 1 Length	35.5 cm
------------------	---------

---

Package 1 Weight	47.25 kg
------------------	----------

---

Unit Type Of Package 2	P12
------------------------	-----

---

Number Of Units In Package 2	6
------------------------------	---

---

Package 2 Height	123 cm
------------------	--------

---

Package 2 Width	80 cm
-----------------	-------

---

Package 2 Length	200 cm
------------------	--------

---

Package 2 Weight	293.5 kg
------------------	----------

## Contractual warranty

---

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

RoHS Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Pro-active compliance (Product out of EU RoHS legal scope)

China RoHS Regulation [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations