

Product datasheet

Specifications



Spacial S3D tspt door w/o mount.plate. H1200xW600xD300 IP66 IK08 RAL7035.

Local distributor code:
392866978

NSYS3D12630T

EAN Code: 3606480159923

Main

Range	Spacial
Product Name	Spacial S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure Nominal Height	1200 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	300 mm
Door Type	Glazed
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Installation Accessory Type	Wall-mounting
Device Composition	1 body 1 door 1 lock 1 cable gland plate

Complementary

Body Type	Single piece body Gutter-shaped front rail double sheet thickness
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Body: steel Door: steel and security glass
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	DNV LR BV GL cUL UL
Net Weight	32 kg

Environment

Electromagnetic Compatibility	Electromagnetic field immunity test
Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK08 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.5 cm
Package 1 Width	62 cm
Package 1 Length	123.5 cm
Package 1 Weight	32 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	199 cm
Package 2 Width	80 cm
Package 2 Length	120 cm
Package 2 Weight	213 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations