# **Product datasheet**

Specifications





# Spacial S3D seismic plain door with mount.plate -H800xW600xD300 - IP65 - IK10

Local distributor code: 402657857

NSYS3D6G8630P

EAN Code: 3606480793981

#### Main

Range	Spacial
Product Name	S3D 6G
Enclosure Application	Seismic
Product Or Component Type	Enclosure
Enclosure Nominal Height	800 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	300 mm
Door Type	Plain
Mounting Plate Description	Reinforce
Enclosure Mounting	Wall mounted
Device Composition	1 x body 1 x door 1 x lock 2 x fixing bracket 1 x mounting plate 1 x earthing components door and lock 1 x cable gland plate
Continuity Of Earth	Earthing connection between body and door

### Complementary

Single piece body Gutter-shaped front rail
Front face: 1 door(s)
Right (120 °)
3-point closure
EDF 1600
Swing handle
Front
Cable gland plate by screws
Steel
Body: 2 mm Door: 2 mm Cable gland plate: 1.5 mm
Epoxy-polyester powder
Grey (RAL 7035)
47 kg

### Environment

Surface Treatment	87 % decontaminable painting conforming to NF T 30-501.	
Standards	IEC 62208 EDF CRT 91 C 112 00	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK10 conforming to IEC 62262	
Seismic Performance	Seismic tests 6G conforming to EDF CRT 91 C 112 00	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	89.0 cm
Package 1 Width	36.0 cm
Package 1 Length	63.0 cm
Package 1 Weight	47.0 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations