Product datasheet

Specifications





Spacial S3D tspt door w/o mount.plate H700xW500xD250.IP66 IK08 RAL7035.

Local distributor code: 392866606

NSYS3D7525T

EAN Code: 3606480159077

Main

| Range | Spacial |
|-----------------------------|---|
| Product Name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 700 mm |
| Enclosure Nominal Width | 500 mm |
| Enclosure Nominal Depth | 250 mm |
| Door Type | Glazed |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Standard |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 1 door 1 lock 1 cable gland plate |

Complementary

| Body Type | Gutter-shaped front rail double sheet thickness Single piece body |
|-----------------------------|--|
| Number Of Doors | Front face: 1 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 points lock, 3 mm double-bar |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Cable gland plate by screws |
| Material | Body: steel Door: steel and security glass |
| Surface Finish | Epoxy-polyester powder |
| Colour | Grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | LR cUL GL DNV BV UL |

Environment

| Electromagnetic Compatibility | Electromagnetic field immunity test |
|-------------------------------|-------------------------------------|
| Nema Degree Of Protection | NEMA 4X/13 |
| Ik Degree Of Protection | IK08 conforming to IEC 62262 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 29.5 cm |
| Package 1 Width | 51 cm |
| Package 1 Length | 65 cm |
| Package 1 Weight | 19.29 kg |
| Unit Type Of Package 2 | РАМ |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 157.6 cm |
| Package 2 Width | 100 cm |
| Package 2 Length | 120 cm |
| Package 2 Weight | 244.5 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |