# **Product datasheet**

Specifications





### Spacial S3D plain door w/o mount.plate. H800xW1000xD300.IP66 IK10 RAL7035.

Local distributor code: 392867100

NSYS3D81030

#### EAN Code: 3606480159060

#### Main

Spacial
Spacial S3D
Multi-purpose
Compact enclosure
800 mm
1000 mm
300 mm
Plain
Without mounting plate
Standard
Wall-mounting
1 body 2 cable gland plate 1 door 1 lock

#### Complementary

Body Type	Gutter-shaped front rail double sheet thickness Single piece body
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Accessibility For Operation	Front
Removable Parts	Door by hinges Cable gland plate by screws
Material	Steel
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	UL GL BV DNV LR cUL
Net Weight	38 kg

### Environment

Nema Degree Of Protection	NEMA 4X/13
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ip Degree Of Protection	IP66 conforming to IEC 60529

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82.0 cm
Package 1 Width	104.0 cm
Package 1 Length	36.0 cm
Package 1 Weight	38.0 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	6
Package 2 Height	120 cm
Package 2 Width	103 cm
Package 2 Length	178 cm
Package 2 Weight	214 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations