Product datasheet

Specifications





Spacial S3D dble plain door with mount.plate. H800xW1000xD300.IP55 IK10 RAL7035.

Local distributor code: 392867126

NSYS3D81030DP

EAN Code: 3606480159046

Main

| mann | |
|-----------------------------|---|
| Range | Spacial |
| Product Name | Spacial S3D |
| Application | Multi-purpose |
| Category | Compact enclosure |
| Enclosure Nominal Height | 800 mm |
| Enclosure Nominal Width | 1000 mm |
| Enclosure Nominal Depth | 300 mm |
| Door Type | Plain |
| Mounting Plate Description | Plain |
| Type Of Gland Plate | Standard |
| Installation Accessory Type | Wall-mounting |
| Device Composition | 1 body 2 cable gland plate 2 door with lock 1 mounting plate |

Complementary

| · · · · · · · · · · · · · · · · · · | |
|-------------------------------------|---|
| Body Type | Single piece body Gutter-shaped front rail double sheet thickness |
| Number Of Doors | Front face: 2 door(s) |
| Door Opening Side | Reversible (120 °) |
| Lock Type | 3 points lock, 3 mm double-bar |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Cable gland plate by screws Mounting plate by fixing element |
| Material | Enclosure: steel Mounting plate: galvanised steel |
| Surface Finish | Enclosure: epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) |
| Standards | IEC 62208 |
| Product Certifications | cUL UL GL DNV BV LR |

| Net Weight | 51 kg |
|-------------------------|------------------------------|
| Environment | |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Packing Units | |
| Unit Type Of Package 1 | PCE |

| Number Of Units In Package 1 | 1 |
|------------------------------|----------|
| Package 1 Height | 36.0 cm |
| Package 1 Width | 82.0 cm |
| Package 1 Length | 102.5 cm |
| Package 1 Weight | 47.6 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 6 |
| Package 2 Height | 180.0 cm |
| Package 2 Width | 102.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 306.0 kg |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |