Product datasheet

Specifications





SPACIAL S3X stainless 316L, Scotch Brite® finish, H1200xW1000xD300 mm.

Local distributor code: 398252793

NSYS3X121030H

EAN Code: 3606480155000

Main

Range	Spacial
Product Name	Spacial S3X
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	1200 mm
Nominal Width	1000 mm
Nominal Depth	300 mm
Product Installation	Wall-mounting
Device Composition	1 body 2 door 1 lock: door 1 reinforcement frame drilled: door

Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 2 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Hinge: stainless steel Body and door: stainless steel 316L
Surface Finish	Body and door: Scotch-Brite® brushed
Net Weight	51.6 kg

Environment

Standards	IEC 62208
Product Certifications	UL 508 type A CAN/CSA 22
Ip Degree Of Protection	IP55 conforming to IEC 60529

Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.0 cm
Package 1 Width	101.5 cm
Package 1 Length	122.0 cm
Package 1 Weight	51.6 kg
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	4
Package 2 Height	140.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	228.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations