# **Product datasheet**

Specification





# SPACIAL S3X stainless 316L, Scotch Brite® finish, H800xW800xD300 mm.

Local distributor code: 398252722

NSYS3X8830H

EAN Code: 3606480155338

#### Main

Range	Spacial	
Product Name	Spacial S3X	
Enclosure Type	Multi-purpose	
Category	Compact enclosure	
Nominal Height	800 mm	
Nominal Width	800 mm	
Nominal Depth	300 mm	
Product Installation	Wall-mounting	
<b>Device Composition</b>	1 body	
	1 door	
	2 lock: door	
	2 perforated vertical profile drilled: door	

### Complementary

Body Type	Single piece body, cross-shaped structure Gutter shaped front rail
Door Type	Plain
Number Of Doors	Front face: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	2 points lock, 3 mm double-bar
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Front
Removable Parts	Door by hinges
Material	Lock: zamak Hinge: stainless steel Body and door: stainless steel 316L
Surface Finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net Weight	32 kg

#### **Environment**

Standards	IEC 62208
Product Certifications	UL 508 type A CAN/CSA 22

Ip Degree Of Protection	IP66 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Environmental Characteristic	Specific hygiene Corrosive

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82.0 cm
Package 1 Width	40.0 cm
Package 1 Length	82.0 cm
Package 1 Weight	32.5 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	8
Package 2 Height	120 cm
Package 2 Width	100 cm
Package 2 Length	180 cm
Package 2 Weight	259 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations