



Price\* : 31.43 GBP



### Main

Range	Spacial
Product name	Spacial SBM
Device application	Multi-purpose
Category	Industrial box
Device short name	SBM
Enclosure type	Flat face box
Enclosure nominal height	150 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	80 mm
Enclosure mounting	Wall mounted
Device composition	4 cover screw 1 cover 1 body
Body type	Single piece body folded and welded
Type of front cover	Plain door
Cover fixing	Half turn metal screw
Lock type	Captive screw PZ2 outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	Sheet steel
Surface finish	Polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	BV LR DNV UL

GL

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for storage	-35...60 °C
Operating temperature	-35...80 °C
Net weight	1.754 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">Download RoHS China Declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------