Product datasheet

Specifications





Metal industrial box plain door H200xW200xD80 IP66 IK10 RAL 7035

Local distributor code: 397088764

NSYSBM20208

EAN Code: 3606480520051

Main

Range	Spacial	
Product Name	Spacial SBM	
Device Application	Multi-purpose	
Category	Industrial box	
Device Short Name	SBM	
Enclosure Type	Flat face box	
Enclosure Nominal Height	200 mm	
Enclosure Nominal Width	200 mm	
Enclosure Nominal Depth	80 mm	
Enclosure Mounting	Wall mounted	
Device Composition	4 cover screw 1 cover 1 body	
Body Type	Single piece body folded and welded	
Type Of Front Cover	Plain door	
Cover Fixing	Half turn metal screw	
Lock Type	Captive screw PZ2 outside sealed area	
Removable Parts	Cover by captive screws	

Complementary

Material	Sheet steel	
Surface Finish	Polyester powder	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	LR DNV-GL UL BV	
Ip Degree Of Protection	IP66 conforming to IEC 60529	
Ik Degree Of Protection	IK10 conforming to IEC 62262	
Ambient Air Temperature For Storage	-3560 °C	
Operating Temperature	-3580 °C	
Net Weight	1.62 kg	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	21.5 cm
Package 1 Length	21.5 cm
Package 1 Weight	1.62 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	38
Package 2 Height	50.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	71.56 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations