# **Product datasheet**

Specifications



(!) Discontinued

### Metal industrial box FL21 cable entry H300xW800xD120 IP55 IK10 RAL 7035

NSYSBMC308012

.

EAN Code: 3606480520389

\_\_\_\_\_

Main	
Range	Spacial
Product Name	Spacial SBM
Device Application	Multi-purpose
Category	Industrial box
Device Short Name	SBMC
Enclosure Type	Entry box
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	120 mm
Enclosure Mounting	Wall mounted
Device Composition	1 cover 1 body 6 cover screw 6 FL21 cable gland plate
Body Type	Single piece body folded and welded
Type Of Front Cover	Plain door
Cover Fixing	Half turn metal screw
Lock Type	Captive screw PZ2 outside sealed area
Removable Parts	Cover by captive screws Cable gland plate screw

#### Complementary

Material	Sheet steel
Surface Finish	Polyester powder
Colour	Grey (RAL 7035)
Standards	IEC 62208
Product Certifications	LR UL DNV GL BV
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Storage	-3560 °C

Operating Temperature	-3580 °C
Net Weight	10.704 kg

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	83 cm
Package 1 Width	33 cm
Package 1 Length	14 cm
Package 1 Weight	10.704 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations