



Metal industrial box FL21 cable entry H400xW400xD120 IP55 IK10 RAL 7035

NSYSBMC404012

EAN Code: 3606480520396



Main

Range	Spacial	
Product Name	Spacial SBM	
Device Application	Multi-purpose	
Category	Industrial box	
Device Short Name	SBMC	
Enclosure Type	Entry box	
Enclosure Nominal Height 400 mm		
Enclosure Nominal Width 400 mm		
Enclosure Nominal Depth	120 mm	
Enclosure Mounting	Wall mounted	
Device Composition	4 cover screw 1 cover 1 body 4 FL21 cable gland plate	
Body Type	Single piece body folded and welded	
Type Of Front Cover	Plain door	
Cover Fixing	Half turn metal screw	
Lock Type	Captive screw PZ2 outside sealed area	
Removable Parts Cover by captive screws Cable gland plate screw		

Complementary

Material	Sheet steel	
Surface Finish	Polyester powder	
Colour	Grey (RAL 7035)	
Standards	IEC 62208	
Product Certifications	UL DNV GL BV LR	
Ip Degree Of Protection	IP55 conforming to IEC 60529	
Ik Degree Of Protection	ection IK10 conforming to IEC 62262	
Ambient Air Temperature For Storage	-3560 °C	

Operating Temperature	-3580 °C
Net Weight	6.532 ka

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42.5 cm
Package 1 Width	42.5 cm
Package 1 Length	14.5 cm
Package 1 Weight	6.532 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations