# **Product datasheet**





### Spacial SF enclosure with mounting plate - assembled -1200x600x600 mm

Local distributor code: 398253462

NSYSF12660P

! Discontinued on: 8 Apr 2024

! To be end-of-service on: 8 Apr 2025

EAN Code: 3606485117393

#### Main

| Range                     | Spacial   |
|---------------------------|---|
| Extended Range            | Spacial SF  |
| Application               | Multi-purpose   |
| Product Or Component Type | Suitable enclosure  |
| Enclosure Nominal Height  | 1200 mm   |
| Enclosure Nominal Width   | 600 mm  |
| Enclosure Nominal Depth   | 600 mm  |
| Enclosure Mounting        | Floor-standing  |
| Device Composition        | 2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate |

### Complementary

| Structure Type              | Perforated structure with a pitch of 25 mm  Vertical uprights joined with top and bottom frames  Panels and doors built into the structure  Formed from a single section |
|-----------------------------|--|
| Door Opening Side           | Reversible (120 °)   |
| Door Type                   | Plain front  |
| Mounting Plate Description  | Plain  |
| Type Of Gland Plate         | Without gland plate  |
| Lock Type                   | 4 points lock, handle with 5 mm double bar insert front door   |
| Number Of Doors             | Front: 1 door(s)   |
| Accessibility For Operation | Sides of enclosure<br>Front<br>Rear  |
| Removable Parts             | Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws         |

Life Is On Schneider 7 May 2024

| Material       | Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass |
|----------------|---|
| Surface Finish | Epoxy-polyester powder  |
| Colour         | Enclosure: grey (RAL 7035)<br>Handle: black (RAL 9005)  |
| Net Weight     | 81.641 kg   |

### **Environment**

| Standards                 | IEC 62208                    |
|---------------------------|------------------------------|
| Nema Degree Of Protection | NEMA 3R/12                   |
| Ip Degree Of Protection   | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection   | IK10 conforming to IEC 62262 |

## **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 64.5 cm  |
| Package 1 Width              | 69.0 cm  |
| Package 1 Length             | 133.0 cm |
| Package 1 Weight             | 67.0 kg  |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |