

Product datasheet

Specifications



Spacial SF PC rack enclosure - assembled - 1600x600x600 mm

Local distributor code:
383615507

NSYSF16660PC

EAN Code: 3606485118741

Main

Range	Spacial
Extended Range	Spacial SF
Application	PC application
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	1600 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	600 mm
Enclosure Mounting	Floor-standing
Product Specific Application	Protecting computer equipment
Device Composition	1 structure 1 roof 2 side panels 1 cable gland plate 1 partial door for keyboard 1 partial door for PC screen 1 partial door for printer support 1 rear door

Complementary

Structure Type	Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure Vertical uprights joined with top and bottom frames
Door Opening Side	Reversible (120 °)
Door Type	Plain partial front Glazed partial front Plain rear
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Cable Entry	1 entry
Number Of Compartiments	3
Lock Type	Flat escutcheon lock, 5 mm double bar rear door Escutcheon lock, 3 mm double bar front partial doors
Number Of Doors	Front: 3 door(s) Rear: 1 door(s)
Accessibility For Operation	Rear Front Sides of enclosure

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Removable Parts	Roof by screws internally Side panel by screws internally Door by screws hinge
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Escutcheon: polyamide 6 with 30 % fibre glass
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

Environment

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262 (of transparent door) IK10 conforming to IEC 62262 (of plain door)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	65.0 cm
Package 1 Width	69.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	127.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations