# **Product datasheet**

Specifications





# Spacial SF enclosure with mounting plate - assembled -2000x1000x400 mm

Local distributor code: 22146081

NSYSF201040P

Discontinued on: 8 Apr 2024

(!) To be end-of-service on: 8 Apr 2025

EAN Code: 3606485117720

#### Main

Range	Spacial
Extended Range	Spacial SF
Application	Multi-purpose
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	1000 mm
Enclosure Nominal Depth	400 mm
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate

### Complementary

Structure Type	Vertical uprights joined with top and bottom frames Formed from a single section Perforated structure with a pitch of 25 mm Panels and doors built into the structure
Door Opening Side	Reversible (120 °)
Door Type	Plain front
Mounting Plate Description	Plain
Type Of Gland Plate	Without gland plate
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Number Of Doors	Front: 1 door(s)
Accessibility For Operation	Rear Sides of enclosure Front
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws

Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net Weight	159.903 kg

### Environment

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	213.0 cm
Package 1 Width	104.0 cm
Package 1 Length	46.0 cm
Package 1 Weight	157.661 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	98 cm
Package 2 Width	105 cm
Package 2 Length	213 cm
Package 2 Weight	290 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations