Product datasheet





Spacial SF enclosure with mounting plate - assembled -2000x600x400 mm

Local distributor code:

22145875 NSYSF20640P

Discontinued on: 11 Apr 2024

! To be end-of-service on: 30 Sept 2025

EAN Code: 3606485117638

Main

Spacial
Spacial SF
Multi-purpose
Suitable enclosure
2000 mm
600 mm
400 mm
Floor-standing
2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 1 mounting plate

Complementary

Structure Type	Formed from a single section
	Panels and doors built into the structure
	Perforated structure with a pitch of 25 mm
	Vertical uprights joined with top and bottom frames
Door Opening Side	Reversible (120 °)
Door Type	Plain front
Mounting Plate Description	Plain
Type Of Gland Plate	Without gland plate
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Number Of Doors	Front: 1 door(s)
Accessibility For Operation	Sides of enclosure
	Rear
	Front
Removable Parts	Door by screws hinge
	Mounting plate by screws mounting plate bracket
	Rear panel by screws
	Roof by screws
	Mounting plate bracket by screws

Life Is On Schneider 2 May 2024

Sliding rail by screws

Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)
Net Weight	102.334 kg

Environment

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.0 cm
Package 1 Width	64.5 cm
Package 1 Length	213.0 cm
Package 1 Weight	103.0 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	213.0 cm
Package 2 Width	65.0 cm
Package 2 Length	98.0 cm
Package 2 Weight	206.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations