Product datasheet

Specification





Spacial SF compartmentalised enclosure - assembled - 2000x600x600 mm

Local distributor code:

385516031

NSYSF20660M

EAN Code: 3606485118789

Main

Range	Spacial
Extended Range	Spacial SFM
Application	Compartmentalised application
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	600 mm
Enclosure Nominal Depth	600 mm
Enclosure Mounting	Floor-standing
Product Specific Application	Insulating the control of a device Reduce the destructive effects of a short-circuit
Device Composition	structure rear panel roof intermediate crossbars panels for modularity: top and bottom

Complementary

Structure Type	Vertical uprights joined with top and bottom frames Perforated structure with a pitch of 25 mm Formed from a single section Panels and doors built into the structure
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear Front Sides of enclosure
Removable Parts	Rear panel by screws Roof by screws
Material	Frame: galvanised steel Uprights: galvanised steel Panels: sheet steel Hinge: zamak
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)

Environment

Standards IEC 62208

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	64.5 cm
Package 1 Width	69.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	66.0 kg

Logistical informations

Country Of Origin FF

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations