Product datasheet

Specifications





Spacial SF enclosure without mounting plate - assembled - 2000x800x500 mm

Local distributor code: 1917558

7558 NSYSF20850

! Discontinued on: 8 Apr 2024

! To be end-of-service on: 8 Apr 2025

EAN Code: 3606485118321

Main

| Range | Spacial |
|---------------------------|--|
| Extended Range | Spacial SF |
| Application | Multi-purpose |
| Product Or Component Type | Suitable enclosure |
| Enclosure Nominal Height | 2000 mm |
| Enclosure Nominal Width | 800 mm |
| Enclosure Nominal Depth | 500 mm |
| Enclosure Mounting | Floor-standing |
| Device Composition | 2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof |

Complementary

| Structure Type | Formed from a single section |
|-----------------------------|--|
| | Panels and doors built into the structure |
| | Vertical uprights joined with top and bottom frames |
| | Perforated structure with a pitch of 25 mm |
| Door Opening Side | Reversible (120 °) |
| Door Type | Plain front |
| Mounting Plate Description | Without mounting plate |
| Type Of Gland Plate | Without gland plate |
| Lock Type | 4 points lock, handle with 5 mm double bar insert front door |
| Number Of Doors | Front: 1 door(s) |
| Accessibility For Operation | Sides of enclosure |
| | Rear |
| | Front |
| Removable Parts | Door by screws hinge |
| | Rear panel by screws |
| | Roof by screws |
| | Mounting plate bracket by screws |
| | Sliding rail by screws |
| | Chang ran by colono |

| Material | Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass |
|----------------|---|
| Surface Finish | Epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) Handle: black (RAL 9005) |
| Net Weight | 98.5 kg |

Environment

| Standards | IEC 62208 |
|---------------------------|------------------------------|
| Nema Degree Of Protection | NEMA 3R/12 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 59 cm |
| Package 1 Width | 84.5 cm |
| Package 1 Length | 213 cm |
| Package 1 Weight | 101 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |