## **Product datasheet**

Specification





# Spacial SF compartmentalised enclosure - assembled - 2000x800x800 mm

Local distributor code: 385516060

NSYSF20880M

EAN Code: 3606485118819

#### Main

Range	Spacial
Extended Range	Spacial SFM
Application	Compartmentalised application
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	2000 mm
Enclosure Nominal Width	800 mm
Enclosure Nominal Depth	800 mm
Enclosure Mounting	Floor-standing
Product Specific Application	Insulating the control of a device Reduce the destructive effects of a short-circuit
Device Composition	structure     rear panel     roof     intermediate crossbars     panels for modularity: top and bottom

## Complementary

Structure Type	Vertical uprights joined with top and bottom frames Perforated structure with a pitch of 25 mm Panels and doors built into the structure Formed from a single section
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear Sides of enclosure Front
Removable Parts	Rear panel by screws Roof by screws
Material	Frame: galvanised steel Uprights: galvanised steel Panels: sheet steel Hinge: zamak
Surface Finish	Epoxy-polyester powder
Colour	Grey (RAL 7035)

#### **Environment**

Standards IEC 62208

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	84.5 cm
Package 1 Width	89.0 cm
Package 1 Length	213.0 cm
Package 1 Weight	85.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations