Product datasheet

Specification





Spacial SM compact enclosure with mounting plate - 1800x800x300 mm

Local distributor code: 383546692 NSYSM18830P

EAN Code: 3606485120218

Main

| Range | Spacial |
|-----------------------------|--|
| Product Name | Spacial SM |
| Product Or Component Type | Compact enclosure |
| Application | Multi-purpose |
| Installation Accessory Type | Floor-standing |
| Device Composition | 1 body 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket 1 mounting plate 1 door |
| Removable Parts | Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws |
| Enclosure Nominal Height | 1800 mm |
| Enclosure Nominal Width | 800 mm |
| Enclosure Nominal Depth | 300 mm |

Complementary

| Number Of Doors | Front: 1 door(s) |
|-----------------------------|---|
| Door Opening Side | Reversible (120 °) |
| Door Type | Plain |
| Lock Type | 4 points lock, handle with 5 mm double bar insert |
| Body Type | Single piece body with welded rear panel Front part forming a rigid frame with welded corners |
| Mounting Plate Description | Plain |
| Type Of Gland Plate | Standard |
| Cable Entry | 1 entry |
| Material | Mounting plate: galvanised steel Body: sheet steel Door: sheet steel Hinge: zamak |
| Surface Finish | Epoxy-polyester powder |
| Colour | Enclosure: grey (RAL 7035) Handle: black (RAL 9005) |
| Accessibility For Operation | Front |
| Net Weight | 95 kg |

Environment

| Standards | IEC 62208 |
|-------------------------|------------------------------|
| Product Certifications | DNV BV UL |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 193.0 cm |
| Package 1 Width | 84.5 cm |
| Package 1 Length | 39.0 cm |
| Package 1 Weight | 95.0 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 78 cm |
| Package 2 Width | 85 cm |
| Package 2 Length | 193 cm |
| Package 2 Weight | 200 kg |

Logistical informations

Country Of Origin ES

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |