Product datasheet

Specifications





SMX 304L stainless monobloc enclosure, H1400xW1000xD300mm, Scotch Brite® finish.

Local distributor code:

398322982 NSYSMX141030

EAN Code: 3606480155710

Main

| Range | Spacial |
|----------------------|---|
| Product Name | Spacial SMX |
| Enclosure Type | Multi-purpose |
| Category | Compact enclosure |
| Nominal Height | 1400 mm |
| Nominal Width | 1000 mm |
| Nominal Depth | 300 mm |
| Product Installation | Floor-standing |
| Device Composition | 1 body 2 door 1 cable gland plate 1 locking system with handle: door 4 mounting plate bracket |

Complementary

| Body Type | Single piece body folded and welded | |
|-----------------------------|--|--|
| Door Type | Plain | |
| Door Opening Side | Reversible (120 °) | |
| Number Of Doors | Front face: 2 door(s) | |
| Lock Type | 3 points lock, handle with 5 mm double-bar insert | |
| Type Of Gland Plate | Plain | |
| Accessibility For Operation | Front | |
| Mounting Plate Description | Without mounting plate | |
| Material | Body and door: stainless steel 304L Handle: zamak Hinge: stainless steel | |
| Removable Parts | Door by hinges Mounting plate bracket by screws Cable gland plate by clips | |
| Surface Finish | Enclosure: Scotch-Brite® brushed Handle: painted | |
| Net Weight | 89 kg | |

Environment

Standards IEC 62208

| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
|------------------------------|-------------------------------|
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |
| Product Certifications | UL 508 CAN/CSA 22 |
| Environmental Characteristic | Specific hygiene Corrosive |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 38.0 cm |
| Package 1 Width | 105.0 cm |
| Package 1 Length | 153.0 cm |
| Package 1 Weight | 88.0 kg |

Logistical informations

Country Of Origin BG

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |