

Product datasheet

Specifications



Stainless 304L PC rack, Micro-beading finishing, H1800xW600xD600mm.

NSYSMX18660PC

⚠ Discontinued on: 24 Jul 2020

⚠ End-of-service on: 6 Jul 2023

⚠ Discontinued

EAN Code: 3606480155802

Main

Range	Spacial
Product Name	Spacial SMX
Enclosure Type	Computer protection PC application
Category	Compact enclosure
Nominal Height	1800 mm
Nominal Width	600 mm
Nominal Depth	600 mm
Product Installation	Floor-standing
Device Composition	1 body 1 cable gland plate 1 partial door for keyboard 1 partial door for PC screen 1 partial door for printer support/CPU 1 rear door

Complementary

Body Type	Single piece body folded and welded
Door Type	Plain partial Plain Glazed partial
Door Opening Side	Reversible (120 °)
Number Of Doors	Front: 2 door(s) Front: 1 door(s) Rear: 1 door(s)
Lock Type	3 mm double-bar lock
Type Of Gland Plate	Plain
Accessibility For Operation	Rear Front
Mounting Plate Description	Without mounting plate
Material	Body and door: stainless steel 304L Hinge: stainless steel Door: Securit glass Lock: zamak

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Removable Parts	Cable gland plate by clips Door by hinges rear Partial doors by hinges front Transparent shutter by screws
Surface Finish	Body and door: micro beaded Securit glass: silkscreened Lock: chromium plated
Net Weight	103 kg

Environment

Standards	IEC 62208
Ip Degree Of Protection	IP55 conforming to IEC 60529 (even with the keyboard drawer open)
Ik Degree Of Protection	IK10 conforming to IEC 62262 (plain door) IK08 conforming to IEC 62262 (glazed door)
Environmental Characteristic	Corrosive Specific hygiene

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	80.0 cm
Package 1 Width	80.0 cm
Package 1 Length	197.0 cm
Package 1 Weight	103.0 kg

Contractual warranty

Warranty	18 months
----------	-----------